


Product data sheet

Specifications

Cable duct - 75 x 50 mm - without cover - grey



AK2GD5075

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 50.00 USD

Main

Product Or Component Type	Cable duct
Accessory / Separate Part Category	Cabling accessories
Range Compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity Per Set	Set of 8

Complementary

Color	Gray RAL 7030)
Fixing Mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	2.95 in (75 mm)
Length	78.74 in (2000 mm)
Width	1.97 in (50 mm)
Net Weight	1.94 lb(US) (0.88 kg)
Total Number Of Wires	240

Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Flame Retardance	V-0 UL 94
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	DIN 43659 VDE 0660 VDE 0506

Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
Gtin	3389110570427
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	2.95 in (7.5 cm)
Package 1 Length	78.74 in (200.0 cm)
Package 1 Weight	30.05 oz (852.0 g)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	512
Package 2 Height	45.28 in (115.0 cm)
Package 2 Width	78.94 in (200.5 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	987.67 lb(US) (448.0 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	8
Package 3 Height	4.13 in (10.5 cm)
Package 3 Width	5.51 in (14.0 cm)
Package 3 Length	78.94 in (200.5 cm)
Package 3 Weight	15.43 lb(US) (7.0 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)