





Straight length, I-Line Busway, 1000A, 600VAC, 3 phase, 3 wire, integral ground bus, Al, plug-in, 8ft

AP2310G8ST

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 6,948.48 USD

## Main

Range Of Product	I-Line
Product Or Component Type	Straight length
Application	Plug-in

# Complementary

Line Rated Current	1000 A
Short Circuit Rating	50 kA
Busbar Material	Aluminium: busbar
Integral Ground/High Short Circuit Bracing	50 percent capacity integral ground bus
Rated Voltage	600 V AC
Number Of Phases	3 phase
Wiring Configuration	3-wire
Length	8 ft (2.44 m)

#### **Environment**

Product Certifications	UL listed file E22182
Standards	CSA C22.2 No 27:1997 IEC 61439-2 UL 857

## Ordering and shipping details

Category	US10PE820322
Discount Schedule	0PE8
Gtin	785901669111
Returnability	No
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.87 in (14.9 cm)
Package 1 Width	5.35 in (13.6 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Length	96.50 in (245.1 cm)
Package 1 Weight	97.60 lb(US) (44.271 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

**Reach Regulation** 

Eu Rohs Directive	Compliant
Eu Rons Directive	'
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

**REACh Declaration**