

# Product data sheet

Specifications

SQUARE D



Straight length, I-Line Busway, 400A, 600VAC, 3 phase, 4 wire, integral ground bus, Al, plug-in, 10ft

AP504G10

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 6,987.96 USD

## Main

Range Of Product	I-Line
Product Or Component Type	Straight length
Application	Plug-in

## Complementary

Line Rated Current	400 A
Short Circuit Rating	22 kA
Busbar Material	Aluminium: busbar
Integral Ground/High Short Circuit Bracing	50 percent capacity integral ground bus
Rated Voltage	600 V AC
Number Of Phases	3 phase
Wiring Configuration	4-wire
Length	10 ft (3.05 m)

## Ordering and shipping details

Category	US10PE820066
Discount Schedule	0PE8
Gtin	785901653448
Returnability	Yes
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	83.00 lb(US) (37.648 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>