
Product data sheet

Specification





Cable end, Linergy TR cable ends, twin conductor, red, 1mmÂ², medium size, 5 sets of 50

AZ5DE010

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.24 USD

Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	Dispenser pack
Quantity Per Set	5 sets of 100
Cable Cross Section	0.00 in² (1 mm²)

Complementary

Cable End Type	Twin conductor
Additional Information	Without marker tag holder
Color	Red
Bezel Material	Halogen-free plastic
Tube Material	Copper ISO 1337
Number Of Cables	2
Awg Gauge	AWG 18
Bezel Size	Ø 3.4 x 5.4 mm
Tube Diameter	0.09 in (2.25 mm)
Length	0.59 in (15 mm)
Tube Length	0.31 in (8 mm)
Net Weight	0.31 lb(US) (0.14 kg)

Environment

Product Certifications	cCSAus
Ambient Air Temperature For Operation	-4221 °F (-20105 °C)

Ordering and shipping details

Category	US1000l22621
Discount Schedule	0001
Gtin	3389110515817

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	US	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.16 in (0.400 cm)
Package 1 Width	0.16 in (0.400 cm)
Package 1 Length	0.55 in (1.400 cm)
Package 1 Weight	0.01 oz (0.200 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	500
Package 2 Height	5.16 in (13.100 cm)
Package 2 Width	2.76 in (7.000 cm)
Package 2 Length	4.92 in (12.500 cm)
Package 2 Weight	4.90 oz (139.000 g)
Unit Type Of Package 3	S04
Number Of Units In Package 3	20000
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	15.75 in (40.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	14.11 lb(US) (6.399 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
②	Toxic Heavy Metal Free
②	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations