





Meter mains, QO, CSED, ringed socket, 400A, semi flush mount, Class 320 manual bypass

CU12L400CB150

- ! Discontinued on: Sep 15, 2023
- ! To be end-of-service on: Dec 31, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Meter Mains
Range Of Product	QO
Includes	Circuit-breaker 1) 2P 150 A 120/240 V AC main supply ready assembled

Complementary

Line Rated Current	400 A
Short-Circuit Current	22 kA
Network Number Of Phases	1
Meter Socket Type	Ringed
Mounting	Semi flush with field installed flange kit Surface (outdoor)
Hub Type	A-L
Electrical Connection	Lugs, service ground Studs, line side
Wire Size	AWG 4250 kcmil aluminium/copper)service ground
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	150 A
Branch Breaker Rating	150 A
Service Feed Location	UG
Bypass Type	Manual bypass Class 320
Height	43.00 in (1092.20 mm)
Width	28.25 in (717.55 mm)
Depth	7.87 in (199.90 mm)
Bus Rating	200.0 A

Environment

Product Certifications UL E-6294

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US1DE3A00022
Discount Schedule	DE3A
Gtin	785901523369
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	42.99 in (109.2 cm)
Package 1 Width	28.27 in (71.8 cm)
Package 1 Length	7.87 in (20 cm)
Package 1 Weight	112.00 lb(US) (50.802 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov