Product data sheet

Specifications



Meter mains, QO, CSED, ringed socket, 400A, surface mount, Class 320 manual bypass

CUM400CB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 8,958.00 USD

Main

Product Or Component Type	Meter Mains
Range Of Product	QO

Complementary

Complementaly	
Line Rated Current	400 A
Short-Circuit Current	25 kA
Network Number Of Phases	1
Meter Socket Type	Ringed
Mounting	Surface Semi flush with field installed flange kit
Number Of Spaces	0
Number Of Circuits	0
Number Of Tandem Breakers	0
Hub Type	A-L
Electrical Connection	Lugs, service ground Studs, line side
Wire Size	AWG 4250 kcmil aluminium)service ground AWG 4250 kcmil copper)service ground
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	400 A
Branch Breaker Rating	200 A
Service Feed Location	UG
Bypass Type	Manual bypass Class 320
Height	43.00 in (1092.20 mm)
Width	28.25 in (717.55 mm)
Depth	7.87 in (199.90 mm)

Environment

Product Certifications

UL E-6294

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	US1DE3A00148
Discount Schedule	DE3A
Gtin	785901539544
Returnability	No
Country Of Origin	US

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	42.99 in (109.2 cm)
Package 1 Width	28.27 in (71.8 cm)
Package 1 Length	7.87 in (20 cm)
Package 1 Weight	115.00 lb(US) (52.163 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov