





Safety switch, double throw, non fusible, 30A, 240 VAC/250 VDC, 2 poles, NEMA 1

C92251

Product availability: Stock - Normally stocked in distribution facility

Price*: 615.00 USD

Main

Product	Double Throw Safety Switch	
Current Rating	30 A	
Certifications	CSA	
Enclosure Rating	NEMA 1 galvannealed steel	
Disconnect Type	Non-fusible disconnect	
Mounting Type	Surface	
Number Of Poles	2	
Voltage Rating	240 V AC	
Wire Size	AWG 12AWG 2 aluminium AWG 14AWG 2 copper	

Complementary

Tightening Torque	45 lbf.in (5.08 N.m) 0.02 in² (13.3 mm²) (AWG 6) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)	
Width	9.75 in (247.65 mm)	
Height	10 in (254.00 mm)	
Depth	4.75 in (120.65 mm)	

Ordering and shipping details

Category	US10DE100153
Discount Schedule	0DE1
Gtin	785901995685
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.88 in (12.4 cm)
Package 1 Width	10.00 in (25.4 cm)
Package 1 Length	10.98 in (27.9 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight

7.30 lb(US) (3.31 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov