Product data sheet

Specifications

SQUARE 🗩





Safety switch, general duty, fusible, 30A, 2 pole, 3hp, 120VAC, NEMA 1, neutral factory installed, consumer packaging

D211NCP

Product availability: Stock - Normally stocked in distribution facility

Price*: 90.00 USD

Main

Cingle Throw Sofety Switch
Single Throw Safety Switch
General duty
Residential
Fusible disconnect switch
Neutral/earth strip 2 x 16 mm ² 5 x 6 mm ²
1 phase
2
30 A
120 V AC
NEMA 1
0.5 hp at 120 V AC 60 Hz for 1 phase motors 2 hp at 120 V AC 60 Hz for 1 phase motors 1.5 hp at 240 V AC 60 Hz for 1 phase motors 3 hp at 240 V AC 60 Hz for 1 phase motors

Complementary

Shout Oinswit Oversent Bating	
Short Circuit Current Rating	10 kA plug
Fuse Type	Plug
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 14AWG 6 copper AWG 12AWG 6 aluminium
Tightening Torque	30 lbf.in (3.39 N.m) 0.000.02 in ² (2.0813.3 mm ²) (AWG 14AWG 6)
Depth	3.63 in (92.20 mm)
Width	6.75 in (171.45 mm)
Height	9.25 in (234.95 mm)
Net Weight	3.09 lb(US) (1.4 kg)

Environment

Certifications

UL listed file E2875

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10CPS01311
Discount Schedule	0CPS
Gtin	047569521546
Returnability	Yes
Country Of Origin	МХ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.60 in (14.224 cm)
Package 1 Width	7.60 in (19.304 cm)
Package 1 Length	10.30 in (26.162 cm)
Package 1 Weight	4.56 lb(US) (2.068 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	84
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	382.98 lb(US) (173.716 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov