Product data sheet





NFC cartridge fuses, TeSys GS, cylindrical 14mm x 51mm, fuse type gG, 500VAC, 4A, without striker, set of 10 parts

DF2EN04



(!) Discontinued on: Jul 12, 2021



Main

| Range Of Product | TeSys fuse-disconnector | |
|--------------------------------|-------------------------|--|
| Product Or Component Type | Cartridge fuse | |
| Device Short Name | DF2 | |
| [Ue] Rated Operational Voltage | 500 V AC | |
| Line Rated Current | 4 A 500 V | |
| Fuse Size | 14 x 51 mm | |
| Fuse Type | NFC | |
| Quantity Per Set | Set of 10 | |

Complementary

| Fuse Curve | GG |
|------------|-----------------------|
| Net Weight | 0.04 lb(US) (0.02 kg) |

Ordering and shipping details

| Category | 22621-IEC PANEL ACCESSORIES | |
|-------------------|-----------------------------|--|
| Discount Schedule | I | |
| Gtin | 3389110502466 | |
| Returnability | No | |

Packing Units

| Unit Type Of Package 1 | PCE | |
|------------------------------|-------------------|--|
| Number Of Units In Package 1 | 1 | |
| Package 1 Height | 0.63 in (1.6 cm) | |
| Package 1 Width | 2.95 in (7.5 cm) | |
| Package 1 Length | 4.13 in (10.5 cm) | |
| Package 1 Weight | 0.63 oz (18 g) | |

Contractual warranty

| Warranty | 18 months |
|----------|-----------|
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|--------------------------------|--|
| ⊘ | Toxic Heavy Metal Free | |
| ⊘ | Mercury Free | |
| ⊘ | Rohs Exemption Information Yes | |
| Ø | Pvc Free | |

Certifications & Standards

| Eu Rohs Directive | Compliant | |
|---------------------------|---|--|
| | EU RoHS Declaration | |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) | |
| Environmental Disclosure | Product Environmental Profile | |
| California Proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov | |