





Safety switch, general duty, fusible, 30A, 2 pole, 7.5hp, 240VAC, NEMA 1, neutral factory installed

D221N

Product availability: Stock - Normally stocked in distribution facility

Price*: 122.00 USD

Main

Product	Single Throw Safety Switch	
Duty Rating	General duty	
Device Application	Residential	
Disconnect Type	Fusible disconnect switch	
Factory Installed Neutral	Neutral (factory installed)	
Phase	1 phase	
Number Of Poles	2	
Current Rating	30 A	
Voltage Rating	240 V AC	
Enclosure Rating Nema	NEMA 1	
Motor Power Hp	otor Power Hp 1.5 hp at 240 V AC 60 Hz for 1 phase motors 3 hp at 240 V AC 60 Hz for 3 phase motors 3 hp at 240 V AC 60 Hz for 1 phase motors 7.5 hp at 240 V AC 60 Hz for 3 phase motors	

Complementary

Short Circuit Current Rating	100 kA maximum depending on fuse H, K or R	
Fuse Type	H, K or R	
Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	3-wire	
Wire Size	AWG 14AWG 6 copper AWG 12AWG 6 aluminium	
Tightening Torque	30 lbf.in (3.39 N.m) 0.000.02 in² (2.0813.3 mm²) (AWG 14AWG 6)	
Depth	3.63 in (92.20 mm)	
Width	7.25 in (184.15 mm)	
Height	9.25 in (234.95 mm)	
Net Weight	16.98 lb(US) (7.7 kg)	

Environment

Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1DE1A00006	
Discount Schedule	nt Schedule DE1A	
Gtin	785901460534	
Returnability	Yes	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.20 in (13.21 cm)
Package 1 Width	6.80 in (17.27 cm)
Package 1 Length	9.20 in (23.36 cm)
Package 1 Weight	4.76 lb(US) (2.16 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	150
Package 2 Height	5.20 in (13.21 cm)
Package 2 Width	6.80 in (17.27 cm)
Package 2 Length	9.20 in (23.36 cm)
Package 2 Weight	712.64 lb(US) (323.25 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	5
Package 3 Height	5.20 in (13.21 cm)
Package 3 Width	6.80 in (17.27 cm)
Package 3 Length	9.20 in (23.36 cm)
Package 3 Weight	23.77 lb(US) (10.78 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
②	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov