# Product data sheet





Safety switch, general duty, fusible, 30A, 3 pole, 7.5hp, 240VAC, NEMA 3R, bolt on provision, neutral factory installed

D321NRBUP

! Discontinued on: Jan 31, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product	Single Throw Safety Switch
Duty Rating	General duty
Device Application	Residential
Disconnect Type	Fusible disconnect switch
Factory Installed Neutral	Neutral (factory installed)
Phase	3 phase
Number Of Poles	3
Current Rating	30 A
Voltage Rating	240 V AC
Enclosure Rating Nema	NEMA 3R
Motor Power Hp	1.5 hp at 240 V AC 60 Hz for 1 phase motors 3 hp at 240 V AC 60 Hz for 3 phase motors 3 hp at 240 V AC 60 Hz for 1 phase motors 7.5 hp at 240 V AC 60 Hz for 3 phase motors

### Complementary

Short Circuit Current Rating	100 kA maximum depending on fuse H, K or R
Fuse Type	H, K or R
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	4-wire (3PH + G)
Wire Size	AWG 14AWG 6 copper AWG 12AWG 6 aluminium
Tightening Torque	30 lbf.in (3.39 N.m) 0.000.02 in² (2.0813.3 mm²) (AWG 14AWG 6)
Depth	3.75 in (95.25 mm)
Width	7.75 in (196.85 mm)
Height	9.63 in (244.60 mm)

#### **Environment**

Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US1DE1A00106
Discount Schedule	DE1A
Gtin	785901023777
Returnability	No
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Mercury Free	
<b>9</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov