





Safety switch, general duty, fusible, 400A, 3 pole, 125hp, 240VAC, NEMA 1, neutral factory installed

D325N

Product availability: Stock - Normally stocked in distribution facility

Price\*: 3,113.00 USD

#### Main

| Product                   | Single Throw Safety Switch  |  |
|---------------------------|---|--|
| Duty Rating               | General duty  |  |
| Device Application        | Residential   |  |
| Disconnect Type           | Fusible disconnect switch   |  |
| Factory Installed Neutral | Neutral (factory installed)   |  |
| Phase                     | 3 phase   |  |
| Number Of Poles           | 3   |  |
| Current Rating            | 400 A   |  |
| Voltage Rating            | 240 V AC  |  |
| Enclosure Rating Nema     | NEMA 1  |  |
| Motor Power Hp            | 50 hp at 240 V AC 60 Hz for 3 phase motors<br>125 hp at 240 V AC 60 Hz for 3 phase motors |  |

### Complementary

**Environment** 

Certifications

| Short Circuit Current Rating | 100 kA maximum depending on fuse H, K, J or R  |
|------------------------------|--|
| Fuse Type                    | H, K, J or R   |
| Mounting Type                | Surface  |
| Electrical Connection        | Lugs   |
| Wiring Configuration         | 4-wire (3PH + G)   |
| Wire Size                    | AWG 1/0600 kcmil aluminium/copper 2 x AWG 1/02 x 300 kcmil aluminium/copper                    |
| Tightening Torque            | 340 lbf.in (38.41 N.m) (AWG 1/0750 kcmil)<br>340 lbf.in (38.41 N.m) (2 x AWG 1/02 x 300 kcmil) |
| Depth                        | 8.88 in (225.55 mm)  |
| Width                        | 24.88 in (631.95 mm)   |
| Height                       | 45.12 in (1146.05 mm)  |
| Net Weight                   | 114.64 lb(US) (52 kg)  |

UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Ordering and shipping details

| Category          | US1DE1A00007 |
|-------------------|--------------|
| Discount Schedule | DE1A         |
| Gtin              | 785901461555 |
| Returnability     | Yes          |
| Country Of Origin | MX           |

# **Packing Units**

| Unit Type Of Package 1       | PCE                       |
|------------------------------|---------------------------|
| Number Of Units In Package 1 | 1                         |
| Package 1 Height             | 11.30 in (28.7 cm)        |
| Package 1 Width              | 25.98 in (66.0 cm)        |
| Package 1 Length             | 47.99 in (121.9 cm)       |
| Package 1 Weight             | 115.00 lb(US) (52.163 kg) |

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| Mercury Free                       |
|------------------------------------|
| Rohs Exemption Information Yes     |
| Pvc Free                           |
| Halogen Free Plastic Parts Product |

#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |
|---------------------------|---|
| Eu Rohs Directive         | Compliant with Exemptions   |
| China Rohs Regulation     | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.  |
| Environmental Disclosure  | Product Environmental Profile   |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |