



Thermistor probe, TeSys LT3, integrated triple probe, 120°C, 0 to 2.5V, bulk qty

DA1TT120

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range Of Product	DA1
Product Or Component Type	Thermistor probe
Device Short Name	DA1TT
Accessory / Separate Part Category	Protection accessory
Quantity Per Set	Set of 10
Ambient Air Temperature For Operation	248 °F (120 °C)

Complementary

[Ui] Rated Insulation Voltage	2500 V	
[Ue] Rated Operational Voltage	<= 2.5 V	
Resistance	250 Ohm per probe 25 °C	
Insulation	Reinforced	
Cable Length	3.28 ft (1 m) between probe and motor terminal plate 9.84 in (250 mm) between probes	
Net Weight	0.02 lb(US) (0.01 kg)	

Environment

Standards IEC 60034-11 Mark A

Ordering and shipping details

Category	US10l1122339	
Discount Schedule	0111	
Gtin	3389110531855	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	3.94 in (10.0 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Length	4.33 in (11.0 cm)
Package 1 Weight	0.35 oz (10.0 g)
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	0.59 in (1.5 cm)
Package 2 Width	3.94 in (10.0 cm)
Package 2 Length	4.33 in (11.0 cm)
Package 2 Weight	3.53 oz (100.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	2.39 lb(US) (1.085 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov