Product data sheet





Cable end, Linergy TR cable ends, single conductor, brown, 10mmÂ2, long size, for clip-in, 10 sets of 100

DZ5CA103

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.78 USD

Main

Range Of Product	Linergy	
Product Or Component Type	Cable end	
Cable End Size	Long	
Standards	NF C 63-023	
Type Of Packing	Bag	
Quantity Per Set	Set of 100	
Cable Cross Section	0.02 in² (10 mm²)	

Complementary

Cable End Type	Single conductor	
Additional Information	For additional marker tag holder	
Color	Brown	
Bezel Material	Halogen-free plastic	
Tube Material	Copper ISO 1337	
Number Of Cables	1	
Awg Gauge	AWG 8	
Bezel Size	Ø 8.4 mm	
Tube Diameter	0.19 in (4.9 mm)	
Length	1.10 in (28 mm)	
Tube Length	0.71 in (18 mm)	
Cad Overall Depth	1.10 in (28 mm)	
Net Weight	0.19 lb(US) (0.085 kg)	

Environment

Ambient Air Temperature For -4...221 °F (-20...105 °C)

Ordering and shipping details

Category	US1000l22621	
Discount Schedule	0001	
Gtin	3389110535570	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	DE	

Packing Units

9		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	0.16 in (0.400 cm)	
Package 1 Width	0.16 in (0.400 cm)	
Package 1 Length	0.55 in (1.400 cm)	
Package 1 Weight	0.02 oz (0.600 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	100	
Package 2 Height	1.57 in (4.000 cm)	
Package 2 Width	3.15 in (8.000 cm)	
Package 2 Length	4.33 in (11.000 cm)	
Package 2 Weight	2.40 oz (68.000 g)	
Unit Type Of Package 3	S03	
Number Of Units In Package 3	10000	
Package 3 Height	11.81 in (30.000 cm)	
Package 3 Width	11.81 in (30.000 cm)	
Package 3 Length	15.75 in (40.000 cm)	
Package 3 Weight	16.52 lb(US) (7.492 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
Ø	Toxic Heavy Metal Free
Ø	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free
②	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	No need of specific recycling operations	