





Circuit breaker, FH, 600V, 50A, 3 pole, mech interlock

FHL36050WB

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

o o in promontary		
Line Rated Current	50 A	
Number Of Poles	3P	
Breaking Capacity Code	н	
Mounting Mode	Unit mount	
Magnetic Hold Current	400 A	
Magnetic Tripping Current	850 A	
Electrical Connection	Lugs, load Lugs, line	
Terminal Identifier	AL100FA	
Tightening Torque	79.66 lbf.in (9 N.m) 0.000.08 in² (2.0853.48 mm²) (AWG 14AWG 1/0) 79.66 lbf.in (9 N.m) 0.010.08 in² (3.3153.48 mm²) (AWG 12AWG 1/0) 44.25 lbf.in (5 N.m) 0.010.01 in² (3.315.26 mm²) (AWG 12AWG 10)	
Height	6.4 in (162.56 mm)	
Width	4.5 in (114.30 mm)	
Depth	4.13 in (104.90 mm)	
Circuit Breaker Application	HACR rated	

Environment

Certifications	UL Listed		
	CSA		

Ordering and shipping details

Category	00903-FAL/FHL 600V
Discount Schedule	DE2
Gtin	00785901589792
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.For more information go to www.p65warnings.ca.gov