Product data sheet

Specifications





Shaft extension, TeSys GS, cross section 5x5mm, L400mm, for switches 30 to 32A

GS2AE81

Product availability: Stock - Normally stocked in distribution facility

Price*: 23.30 USD

Main

| Range | TeSys |
|---------------------------------------|------------------------|
| | |
| Device Short Name | GS2AE |
| Product Or Component Type | Shaft extension |
| Accessory / Separate Part Category | Control accessory |
| Range Compatibility | TeSys TeSys GS GS1D |
| | TeSys TeSys GS GS2D |
| | FuPact FuPacT GS GSB32 |
| | FuPact FuPacT GS GSC32 |
| Switch Rated Current | 30 A |
| | 32 A |

Complementary

| Length | 15.75 in (400 mm) |
|---------------------|-----------------------|
| Shaft Cross Section | 5 x 5 mm |
| Net Weight | 0.33 lb(US) (0.15 kg) |

Ordering and shipping details

| Category | US10I1122640 | |
|-------------------|---------------|--|
| Discount Schedule | 0111 | |
| Gtin | 3389119412018 | |
| Returnability | Yes | |
| Country Of Origin | US | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 0.79 in (2.000 cm) |
| Package 1 Width | 3.15 in (8.000 cm) |
| Package 1 Length | 15.75 in (40.000 cm) |
| Package 1 Weight | 4.59 oz (130.000 g) |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 12 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 2 Height | 5.91 in (15.000 cm) |
|------------------|------------------------|
| Package 2 Width | 11.81 in (30.000 cm) |
| Package 2 Length | 15.75 in (40.000 cm) |
| Package 2 Weight | 4.03 lb(US) (1.830 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ② | Toxic Heavy Metal Free | |
| 9 | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| California Proposition 65 | WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
|---------------------------|--|
| Circularity Profile | End of Life Information |
| Environmental Disclosure | Product Environmental Profile |
| China Rohs Regulation | China RoHS declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| Reach Regulation | REACh Declaration |