Product data sheet

Specifications





TeSys GV2, surface mount enclosure, for TeSys GV2ME, IP41 rated

GV2MC01

Product availability: Stock - Normally stocked in distribution

Price*: 54.00 USD

Main

Range	Ta Cura
Kange	TeSys
Product Or Component Type	Enclosure
Device Short Name	GV2MC
Accessory / Separate Part Category	Mounting accessory
Product Compatibility	GV2ME
Enclosure Type	Surface mounting

Complementary

Auxiliary Mounting Location	Left Right
Height	5.79 in (147 mm)
Width	3.66 in (93 mm)
Depth	3.31 in (84 mm)

Environment

Ip Degree Of Protection	IP41
Environmental Characteristic	Standard environment

Ordering and shipping details

Category	US10I1122367
Discount Schedule	0111
Gtin	3389110213645
Returnability	Yes
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.94 in (10 cm)
Package 1 Width	3.94 in (10 cm)
Package 1 Length	5.98 in (15.2 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight	9.28 oz (263 g)
Unit Type Of Package 2	S04
Number Of Units In Package 2	27
Package 2 Height	11.81 in (30 cm)
Package 2 Width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Package 2 Weight	18.21 lb(US) (8.258 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	108
Package 3 Height	31.50 in (80 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	92.40 lb(US) (41.912 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
Ø	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov