## Product data sheet

Specifications





# Flush mounting enclosure for TeSys GV2ME, IP41

GV2MP01

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 31.10 USD

#### Main

Range	TeSys
Product Or Component Type	Enclosure
Device Short Name	GV2MP
Accessory / Separate Part Category	Mounting accessory
Product Compatibility	GV2ME
Enclosure Type	Flush mounting

## Complementary

Auxiliary Mounting Location	Left Right
Height	5.51 in (140 mm)
Width	4.19 in (106.5 mm)
Depth	3.27 in (83 mm)
Net Weight	0.25 lb(US) (0.115 kg)

### Environment

Ip Degree Of Protection	IP41 front face
Environmental Characteristic	Standard environment

## Ordering and shipping details

Category	US10I1122367
Discount Schedule	0111
Gtin	3389110213638
Returnability	Yes
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.53 in (11.5 cm)
Package 1 Width	3.94 in (10 cm)
Package 1 Length	5.91 in (15 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Weight	7.72 oz (219 g)
Unit Type Of Package 2	S04
Number Of Units In Package 2	27
Package 2 Height	11.81 in (30 cm)
Package 2 Width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Package 2 Weight	14.51 lb(US) (6.58 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	108
Package 3 Height	29.53 in (75 cm)
Package 3 Width	23.62 in (60 cm)
Package 3 Length	31.50 in (80 cm)
Package 3 Weight	76.77 lb(US) (34.82 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov