Product data sheet

Specifications





TeSys GV, top feed terminal block, for busbars, 3 P, for TeSys D and TeSys U

GV1G09

Product availability: Stock - Normally stocked in distribution facility

Price*: 34.10 USD

Main

Range	Linergy	
Product Name	FT	
Device Short Name	GV1G	
Product Or Component Type	Terminal block	
Accessory / Separate Part Category	Connection accessory	
Poles Description	3P	
Range Compatibility	TeSys GV2 TeSys Deca TeSys U TeSys U	

Complementary

[le] Rated Operational Current	63 A	
Mounting Location	Тор	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
[Ui] Rated Insulation Voltage	690 V IEC 60947-1	
Connections - Terminals	screw clamp terminals 1 solid AWG 4 screw clamp terminals 1 0.000.02 in² (1.516 mm²) flexible with cable end screw clamp terminals 1 0.000.02 in² (1.516 mm²) flexible without cable end screw clamp terminals 1 0.000.04 in² (1.525 mm²) solid screw clamp terminals 2 0.000.01 in² (1.54 mm²) flexible with cable end screw clamp terminals 2 0.000.01 in² (1.56 mm²) solid screw clamp terminals 2 0.000.01 in² (1.54 mm²) flexible without cable end screw clamp terminals 1 flexible AWG 4	
Tightening Torque	15.05 lbf.in (1.7 N.m) screw clamp terminals 19.47 lbf.in (2.2 N.m) connector	
Net Weight	0.09 lb(US) (0.04 kg)	

Environment

Product Certifications	CE
	UKCA

Ordering and shipping details

Category	US10I1122366
Discount Schedule	0111
Gtin	3389110212570

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes	
Country Of Origin	RO	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.57 in (4 cm)
Package 1 Width	1.97 in (5 cm)
Package 1 Length	2.17 in (5.5 cm)
Package 1 Weight	1.69 oz (48 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	70
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	8.11 lb(US) (3.678 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	1120
Package 3 Height	30.31 in (77 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	150.31 lb(US) (68.18 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	

Dimensions Drawings

Sets of Busbars $\mathsf{GV2G}_{\bullet\bullet\bullet}$ with Terminal Block $\mathsf{GV1G09}$

