# Product data sheet

Specifications





# TeSys GV2, surface mount enclosure, for TeSys GV2ME, IP55 rated

GV2MC02

Product availability: Stock - Normally stocked in distribution

Price\*: 78.00 USD

### Main

Range	TeSys
Product Or Component Type	Enclosure
Device Short Name	GV2MC
Accessory / Separate Part Category	Mounting accessory
Product Compatibility	GV2ME
Enclosure Type	Surface mounting

### Complementary

Auxiliary Mounting Location	Left Right
Height	5.79 in (147 mm)
Width	3.66 in (93 mm)
Depth	3.31 in (84 mm)
Net Weight	0 66 lb(US) (0.3 kg)

#### **Environment**

Ip Degree Of Protection	IP55	
Environmental Characteristic	Standard environment	
Product Certifications	UKCA	

# Ordering and shipping details

Category	US10I1122367	
Discount Schedule	0111	
Gtin	3389110213652	
Returnability	Yes	
Country Of Origin	MX	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.94 in (10.000 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	3.94 in (10.000 cm)
Package 1 Length	6.10 in (15.500 cm)
Package 1 Weight	10.37 oz (294.000 g)
Unit Type Of Package 2	S04
Number Of Units In Package 2	27
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	19.10 lb(US) (8.662 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	108
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	100.97 lb(US) (45.800 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>②</b>	Toxic Heavy Metal Free	
	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov