Product data sheet

Specifications

| SQUARE D | |
|-------------------------------|----------------|
| Green Premium [™] | |
| | • |
| | |
| | |
| | ① Discontinued |

Box, I-Line Panelboard, HCM, 32in W x 48in H x 8.25in D, Type 3R/ 5/12, w/front

HC3248WP

Discontinued on: May 24, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | I-Line |
|---------------------------|------------|
| Product Or Component Type | Enclosure |
| Device Application | Panelboard |
| Device Short Name | HCM |

Complementary

| Line Rated Current | 400 A |
|--------------------------|--------------------------|
| | 800 A |
| | 225 A |
| | 600 A |
| Enclosure Nominal Width | 32.01 in (813 mm) |
| Enclosure Nominal Height | 47.99 in (1219 mm) |
| Enclosure Nominal Depth | 8.27 in (210 mm) |
| | 9.49 in (241 mm) |
| Net Weight | 250.00 lb(US) (113.4 kg) |
| Height | 48 in (1219.20 mm) |
| Depth | 8.25 in (209.55 mm) |

Environment

| Nema Degree Of Protection | NEMA 3R/12 |
|---------------------------|------------|
| Standards | UL CSA |

Ordering and shipping details

| Category | US1PE1A00110 |
|-------------------|--------------|
| Discount Schedule | PE1A |
| Gtin | 785901056850 |
| Returnability | No |
| Country Of Origin | US |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1 |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Package 1 Height | 18.50 in (47 cm) |
|------------------|----------------------------|
| Package 1 Width | 45.00 in (114.3 cm) |
| Package 1 Length | 60.00 in (152.4 cm) |
| Package 1 Weight | 250.00 lb(US) (113.398 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |