Product data sheet

Specifications



Safety switch, heavy duty, fusible, 200A, 4 pole, 150hp, 600VAC/DC, NEMA 1

H464

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,957.00 USD

Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	None
Phase	3 phase
Number Of Poles	4
Current Rating	200 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 1 steel
Motor Power Hp	50 hp at 480 V AC 50-60 Hz for 2 phases motors 125 hp at 480 V AC 50-60 Hz for 2 phases motors 60 hp at 600 V AC 50-60 Hz for 2 phases motors 150 hp at 600 V AC 50-60 Hz for 2 phases motors 40 hp at 250 V DC 50 hp at 600 V DC

Complementary

Short-Circuit Current	10 kA for H or K 200 kA for R or J
Fuse Type	H or K
	R or J
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	4-wire
Wire Size	AWG 6250 kcmil copper or aluminium
Tightening Torque	275 lbf.in (31.07 N.m) 0.020.20 in² (13.3127 mm²) (AWG 6250 kcmil)
Depth	8.75 in (222.25 mm)
Width	24.88 in (631.95 mm)
Height	29 in (736.60 mm)
Net Weight	85.98 lb(US) (39 kg)
Net Weight	85.98 lb(US) (39 kg)

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

UL listed file E2875

Ordering and shipping details

Category	US10DE100008
Discount Schedule	0DE1
Gtin	785901482512
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.13 in (18.11 cm)
Package 1 Width	16.50 in (41.91 cm)
Package 1 Length	26.00 in (66.04 cm)
Package 1 Weight	46.00 lb(US) (20.865 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov