

# Product data sheet

Specifications

SQUARE D

Green Premium™



Mini circuit breaker, Homeline,  
30A, 1 pole, 120/240VAC, 10kA  
AIR, standard type, plug in, UL

HOM130

Product availability: Stock - Normally stocked in distribution facility

Price\*: 26.30 USD

## Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	30 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Short Circuit Current Rating	10 kA
Number Of Spaces	1
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Clamp terminal for 2 cables
Wire Size	1 x AWG 14...AWG 8 ( aluminium/copper ) 2 x AWG 14...AWG 10 ( copper )

## Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.00...0.01 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) (AWG 14...AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

## Environment

Ambient Air Temperature For Operation	104 °F (40 °C)
---------------------------------------	----------------

## Ordering and shipping details

Category	US1DE3D00046
Discount Schedule	DE3D
Gtin	785901065227
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.80 in (2.03 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	2.90 in (7.37 cm)
Package 1 Weight	5.60 oz (158.76 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.20 in (8.128 cm)
Package 2 Width	2.50 in (6.35 cm)
Package 2 Length	10.20 in (25.908 cm)
Package 2 Weight	3.51 lb(US) (1.59 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	10.60 in (26.924 cm)
Package 3 Width	6.90 in (17.526 cm)
Package 3 Length	16.60 in (42.164 cm)
Package 3 Weight	35.05 lb(US) (15.9 kg)

## Contractual warranty

Warranty	Lifetime
----------	----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations