





Tandem circuit breaker, Homeline, 2 x 1 pole at 20A, 120/240VAC, 10kA AIR, plug in, UL

HOMT2020

Product availability: Stock - Normally stocked in distribution facility

Price*: 52.00 USD

Main

Product	Miniature circuit-breaker	
Range	Homeline	
Current Rating	20 A	
Certifications	UL Listed	
Voltage Rating	120/240 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Short Circuit Current Rating	10 kA	
Number Of Spaces	Of Spaces 1	
Circuit Breaker Type	Tandem	
Ratings	HACR rated	
Electrical Connection	Box lugs	
Wire Size	1 x AWG 14AWG 8 (aluminium/copper)	

Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 8)	
Height	3.13 in (79.50 mm)	
Width	1 in (25.40 mm)	
Depth	2.98 in (75.69 mm)	

Environment

Ambient Air Temperature For $\,$ 104 °F (40 °C) Operation

Ordering and shipping details

Category	US1DE3D00046	
Discount Schedule	DE3D	
Gtin	785901065401	
Returnability	Yes	
Country Of Origin	MX	

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	3.00 in (7.62 cm)	
Package 1 Width	1.00 in (2.54 cm)	
Package 1 Length	3.30 in (8.382 cm)	
Package 1 Weight	7.20 oz (204.117 g)	
Unit Type Of Package 2	Type Of Package 2 BB1	
Number Of Units In Package 2	10	
Package 2 Height	3.80 in (9.652 cm)	
Package 2 Width	1.00 in (2.54 cm)	
Package 2 Length	10.40 in (26.416 cm)	
Package 2 Weight	4.55 lb(US) (2.064 kg)	
Unit Type Of Package 3	PAL	
Number Of Units In Package 3	3600	
Package 3 Height	40.00 in (101.6 cm)	
Package 3 Width	40.00 in (101.6 cm)	
Package 3 Length	48.00 in (121.92 cm)	
Package 3 Weight	1656.00 lb(US) (751.148 kg)	

Contractual warranty

Warranty Lifetime



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations