Product data sheet

Specifications







Tandem circuit breaker, Homeline, 2 x 1 pole at 20A, 1 x 2 pole at 30A, 120/240VAC, 10kA AIR, plug in, UL

HOMT2020230

Product availability: Stock - Normally stocked in distribution facility

Price*: 120.00 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	30 A 20 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	1P 2P
Short Circuit Current Rating	10 kA
Number Of Spaces	2
Circuit Breaker Type	Quad tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 14AWG 8 (aluminium/copper)

Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.01 in ² (2.56 mm ²) (AWG 14AWG 8)	
Height	3.13 in (79.50 mm)	
Width	2 in (50.80 mm)	
Depth	2.98 in (75.69 mm)	

Environment

Ambient Air Temperature For $$104\ ^\circ F\ (40\ ^\circ C)$$ Operation

Ordering and shipping details

Category	US1DE3D00046
Discount Schedule	DE3D
Gtin	785901101031
Returnability	Yes

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country	Of	Origin	
---------	----	--------	--

Packing Units

r acking Onits	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	13.60 oz (385.554 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	3.30 in (8.382 cm)
Package 2 Width	2.00 in (5.08 cm)
Package 2 Length	10.20 in (25.908 cm)
Package 2 Weight	4.44 lb(US) (2.014 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	50
Package 3 Height	10.90 in (27.686 cm)
Package 3 Width	7.90 in (20.066 cm)
Package 3 Length	17.40 in (44.196 cm)
Package 3 Weight	45.80 lb(US) (20.775 kg)

Contractual warranty

Warranty

Lifetime

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	