





Mini circuit breaker, Homeline, 20A, 1 pole, 120VAC, 10kA AIR, ground fault class B, plug in, UL

HOM120EPD

Product availability: Stock - Normally stocked in distribution

Price*: 374.00 USD

Main

Product	Miniature circuit-breaker	
Range	Homeline	
Current Rating	20 A	
Certifications	fications UL Listed	
Voltage Rating	120 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Short Circuit Current Rating	10 kA	
Number Of Spaces	1	
Circuit Breaker Type	Type Ground fault protecting class B 30 mA	
Ratings	HACR rated	
Electrical Connection	on Screw clamp terminals	
Wire Size	ze 1 x AWG 14AWG 8 (aluminium/copper)	

Complementary

Tightening Torque 35.40 lbf.in (4.0 N.m) 0.00...0.01 in² (2.5...6 mm²) (AWG 14...AWG 8)

Environment

Ambient Air Temperature For 104 °F (40 °C)

Ordering and shipping details

Category	US1DE3D00143	
Discount Schedule	DE3D	
Gtin	785901636502	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.30 in (3.302 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	3.90 in (9.906 cm)
Package 1 Length	5.50 in (13.97 cm)
Package 1 Weight	9.76 oz (276.691 g)

Contractual warranty

Warranty Lifetime



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov