



Safety switch, heavy duty, non fusible, 60A, 3 pole, 60hp, 600VAC/DC, NEMA 12, interlock kit

HU362AWKEI2



(!) Discontinued on: Jun 23, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Single Throw Safety Switch
Heavy duty
Heavy application
Non-fusible disconnect
None
3 phase
3
60 A
600 V AC/DC
NEMA 3R/12
10 hp at 240 V AC 50-60 Hz for 1 phase motors 20 hp at 240 V AC 50-60 Hz for 3 phase motors 25 hp at 480 V AC 50-60 Hz for 1 phase motors 50 hp at 480 V AC 50-60 Hz for 3 phase motors 30 hp at 600 V AC 50-60 Hz for 1 phase motors 60 hp at 600 V AC 50-60 Hz for 3 phase motors 10 hp at 250 V DC 30 hp at 600 V DC

Complementary

Mounting Type	Surface
Wiring Configuration	3-wire
Wire Size	AWG 14AWG 3 copper AWG 12AWG 3 aluminium
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 3) 45 lbf.in (5.08 N.m) (AWG 6AWG 4) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 50 lbf.in (5.65 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)
Depth	7 in (177.80 mm)
Width	10.5 in (266.70 mm)
Height	16.5 in (419.10 mm)

Environment

Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100160
Discount Schedule	0DE1
Gtin	785901077930
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.50 in (41.9 cm)
Package 1 Width	10.51 in (26.7 cm)
Package 1 Length	7.01 in (17.8 cm)
Package 1 Weight	19.20 lb(US) (8.709 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov