





Safety switch, heavy duty, non fusible, 200A, 4 pole, 150HP, 600V AC/DC, NEMA 12

HU464AWK

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 2,832.00 USD

### Main

Single Throw Safety Switch	
Heavy duty	
Heavy application	
Non-fusible disconnect	
None	
3 phase	
4	
200 A	
600 V AC/DC	
NEMA 3R/12 galvannealed steel	
50 hp at 240 V AC 50-60 Hz for 2 phases motors 60 hp at 240 V AC 50-60 Hz for 3 phase motors 50 hp at 480 V AC 50-60 Hz for 2 phases motors 125 hp at 480 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V AC 50-60 Hz for 2 phases motors 150 hp at 600 V AC 50-60 Hz for 3 phase motors 150 hp at 600 V AC 50-60 Hz for 3 phase motors 40 hp at 250 V DC 50 hp at 600 V DC	

### Complementary

Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	4-wire	
Wire Size	AWG 6250 kcmil copper or aluminium	
Tightening Torque	275 lbf.in (31.07 N.m) 0.020.20 in² (13.3127 mm²) (AWG 6250 kcmil)	
Depth	8.75 in (222.25 mm)	
Width	18.63 in (473.20 mm)	
Height	29 in (736.60 mm)	
Net Weight	80.49 lb(US) (36.51 kg)	

### **Environment**

Certifications UL listed file E2875

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US10DE100116	
Discount Schedule	0DE1	
Gtin	785901505976	
Returnability	Yes	
Country Of Origin	US	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.00 in (63.5 cm)
Package 1 Width	7.13 in (18.11 cm)
Package 1 Length	16.50 in (41.91 cm)
Package 1 Weight	54.95 lb(US) (24.925 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov