





Mini circuit breaker, Homeline, 40A, 2 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL

HOM240

Product availability: Stock - Normally stocked in distribution

Price*: 60.00 USD

Main

Product	Miniature circuit-breaker	
Range	Homeline	
Current Rating	40 A	
Certifications	ations UL Listed	
Voltage Rating	ge Rating 120/240 V AC	
Mounting Type	nting Type Plug-in	
Number Of Poles	2P	
Short Circuit Current Rating	10 kA	
Number Of Spaces	2	
Circuit Breaker Type	Breaker Type Standard	
Ratings	HACR rated	
Electrical Connection	Box lugs	
Wire Size	1 x AWG 8AWG 2 (aluminium/copper)	

Complementary

Tightening Torque	40.71 lbf.in (4.6 N.m) (AWG 8AWG 2)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature For 104 °F (40 °C) Operation

Ordering and shipping details

Category	US1DE3D00046
Discount Schedule	DE3D
Gtin	785901065302
Returnability	Yes
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.60 in (4.06 cm)	
Package 1 Width	2.60 in (6.6 cm)	
Package 1 Length	1 Length 3.10 in (7.87 cm)	
Package 1 Weight	1 Weight 11.20 oz (317.52 g)	
Unit Type Of Package 2	pe Of Package 2 BB1	
Number Of Units In Package 2	Of Units In Package 2 5	
Package 2 Height	2 Height 3.20 in (8.128 cm)	
Package 2 Width	2 Width 2.60 in (6.604 cm)	
Package 2 Length	Length 10.20 in (25.908 cm)	
Package 2 Weight	Veight 3.58 lb(US) (1.624 kg)	
Unit Type Of Package 3	Of Package 3 CAR	
Number Of Units In Package 3	Of Units In Package 3 50	
Package 3 Height	3 Height 10.40 in (26.416 cm)	
Package 3 Width	e 3 Width 6.90 in (17.526 cm)	
Package 3 Length	Length 16.60 in (42.164 cm)	
Package 3 Weight 36.65 lb(US) (16.624 kg)		

Contractual warranty

Warranty Lifetime



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations