





Tandem circuit breaker, Homeline, 2 x 1 pole at 15A, 120/240VAC, 10kA AIR, plug in, UL

HOMT1515

Product availability: Stock - Normally stocked in distribution

Price*: 52.00 USD

Main

Product	Miniature circuit-breaker	
Range	Homeline	
Current Rating	15 A	
Certifications	ns UL Listed	
Voltage Rating	120/240 V AC	
Mounting Type	g Type Plug-in	
Number Of Poles	1P	
Short Circuit Current Rating	10 kA	
Number Of Spaces	1	
Circuit Breaker Type	eaker Type Tandem	
Ratings	HACR rated	
Electrical Connection	cal Connection Box lugs	
Wire Size	Size 1 x AWG 14AWG 8 (aluminium/copper)	

Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature For $\,$ 104 °F (40 °C) Operation

Ordering and shipping details

Category	US1DE3D00046
Discount Schedule	DE3D
Gtin	785901065388
Returnability	Yes
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	7.20 oz (204.117 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.30 in (8.382 cm)
Package 2 Width	2.60 in (6.604 cm)
Package 2 Length	10.10 in (25.654 cm)
Package 2 Weight	4.50 lb(US) (2.041 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	3600
Package 3 Height	40.00 in (101.6 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	1648.00 lb(US) (747.52 kg)

Contractual warranty

Warranty Lifetime



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations