





Automatic switch, PowerPacT J, 225A, 3 pole, 600VAC, 50kA, plug in, magnetic, aux

JLN36000S25AB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 3,707.00 USD

### Main

Product Or Component Type	Automatic switch
Range Of Product	PowerPact J
Trip Unit Technology	Magnetic
Accessory / Separate Part Type	Auxiliary switch 2 NO + 2 NC

### Complementary

Line Rated Current	250 A
[Ue] Rated Operational Voltage	600 V AC
	250 V DC
Mounting Mode	Plug-in
Poles Description	3P
Short-Circuit Withstand	125 kA 240 V UL 489
	100 kA 480 V UL 489
	50 kA 600 V UL 489
	20 kA 250 V UL 489
Breaking Capacity Code	L
Electrical Connection	Plug-in, line
	Plug-in, load
Awg Gauge	x AWG 3/0350 kcmil ( aluminium/copper )
Terminal Identifier	AL250JD
Magnetic Tripping Current	3125 A
Height	7.52 in (191.01 mm)
Width	4.12 in (104.65 mm)
Depth	5 in (127.00 mm)
Tightening Torque	230.12 lbf.in (26 N.m) 0.150.29 in² (95185 mm²) (AWG 3/0350 kcmil)

### **Environment**

<b>Product Certifications</b>	CE	
	UL Listed	
	NMX	
	CSA	
	CCC	
	IEC	

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US10DE201120
Discount Schedule	0DE2
Gtin	785901886402
Returnability	No
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.80 in (12.192 cm)
Package 1 Width	11.00 in (27.94 cm)
Package 1 Length	14.50 in (36.83 cm)
Package 1 Weight	5.00 lb(US) (2.268 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov