





Safety switch, heavy duty, non fusible, 100A, 3 pole, 100HP, 600V AC/DC, NEMA 4, 4X, 5, 304 stainless steel, interlock kit

HU363DSEI

(!)

(!) Discontinued on: Jan 31, 2024



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Non-fusible disconnect	
Factory Installed Neutral	None	
Phase	3 phase	
Number Of Poles	3	
Current Rating	100 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	NEMA 4/4X/5 stainless steel 304	
Motor Power Hp	20 hp at 240 V AC 50-60 Hz for 1 phase motors 40 hp at 240 V AC 50-60 Hz for 3 phase motors 40 hp at 480 V AC 50-60 Hz for 1 phase motors 75 hp at 480 V AC 50-60 Hz for 3 phase motors 40 hp at 600 V AC 50-60 Hz for 1 phase motors 100 hp at 600 V AC 50-60 Hz for 1 phase motors 20 hp at 250 V DC 50 hp at 600 V DC	

Complementary

Mounting Type	Surface
Wiring Configuration	3-wire
Wire Size	AWG 12AWG 1/0 aluminium AWG 14AWG 1/0 copper
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 1AWG 3/0) 45 lbf.in (5.08 N.m) (AWG 6AWG 4) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)
Depth	6.97 in (177.04 mm)
Width	11.25 in (285.75 mm)
Height	20.82 in (528.83 mm)
Net Weight	22.33 lb(US) (10.13 kg)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100010
Discount Schedule	0DE1
Gtin	785901078012
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.70 in (19.558 cm)
Package 1 Width	11.70 in (29.718 cm)
Package 1 Length	23.40 in (59.436 cm)
Package 1 Weight	22.00 lb(US) (9.979 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov