# Product data sheet

Specifications



### Safety switch, heavy duty, non fusible, 200A, 3 wire, 3 pole, 150HP, 600V AC/DC, NEMA 12

HU364AWK

Discontinued on: Nov 22, 2023

Product availability: Stock - Normally stocked in distribution facility

Μ	ai	in

Single Throw Safety Switch
Heavy duty
Heavy application
Non-fusible disconnect
None
3 phase
3
200 A
600 V AC/DC
NEMA 3R/12 galvannealed steel
15 hp at 240 V AC 50-60 Hz for 1 phase motors 60 hp at 240 V AC 50-60 Hz for 3 phase motors 50 hp at 480 V AC 50-60 Hz for 1 phase motors 125 hp at 480 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V AC 50-60 Hz for 1 phase motors 150 hp at 600 V AC 50-60 Hz for 3 phase motors 40 hp at 250 V DC 50 hp at 600 V DC

### Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 6250 kcmil copper or aluminium
Tightening Torque	275 lbf.in (31.07 N.m) 0.020.20 in² (13.3127 mm²) (AWG 6250 kcmil)
Depth	8.75 in (222.25 mm)
Width	18.63 in (473.20 mm)
Height	29 in (736.60 mm)
Net Weight	52.01 lb(US) (23.59 kg)

#### Environment

Certifications

UL listed file E2875

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	US10DE100113
Discount Schedule	0DE1
Gtin	785901505778
Returnability	Yes
Country Of Origin	US

# **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.20 in (23.368 cm)
Package 1 Width	19.50 in (49.53 cm)
Package 1 Length	32.50 in (82.55 cm)
Package 1 Weight	51.33 lb(US) (23.283 kg)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Compliant EU RoHS Declaration China RoHS declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
lo need of specific recycling operations
VARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth lefects or other reproductive harm. For more information go to ww.P65Warnings.ca.gov