# Product data sheet

Specifications





# Suppressor module, TeSys Deca, diodes, 12 to 250VDC

LA4DC1U

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 31.44 USD

#### Main

Range	TeSys
Device Short Name	LA4D
Product Or Component Type	Suppressor module
Product Compatibility	3P LP1D09LP1D32

#### Complementary

Mounting Mode	By screws
Suppressor Technology	Flywheel diode
[Uc] Control Circuit Voltage	24250 V DC
Maximum Peak Voltage	1 Uc

#### Environment

Ambient Air Temperature For Operation	-13131 °F (-2555 °C)
Ambient Air Temperature For Storage	-40176 °F (-4080 °C)

## Ordering and shipping details

Category	US10I1222341
Discount Schedule	0112
Gtin	3389110233162
Returnability	No
Country Of Origin	US

## **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.10 in (2.8 cm)
Package 1 Width	1.65 in (4.2 cm)
Package 1 Length	2.01 in (5.1 cm)
Package 1 Weight	0.49 oz (14.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	78

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	2.88 lb(US) (1.308 kg)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

# Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations