

# Product data sheet

Specifications



Circuit breaker enclosure,  
PowerPacT H/J, 15A to 250A,  
NEMA 1, flush mount, 15.42in W x  
32.5in H x 6in D

J250F

Product availability: Stock - Normally stocked in distribution facility

Price\*: 342.00 USD

## Main

Breaker Compatibility	Circuit breaker H-Frame 15...250 A Circuit breaker J-Frame 15...250 A
-----------------------	--

## Complementary

Height	32.5 in (825.50 mm)
Width	15.42 in (391.67 mm)
Depth	6 in (152.40 mm)

## Environmental

Nema Degree Of Protection	NEMA 1
---------------------------	--------

## Ordering and shipping details

Category	US10DE100030
Discount Schedule	0DE1
Gtin	785901417286
Returnability	Yes
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.01 in (17.8 cm)
Package 1 Width	16.18 in (41.1 cm)
Package 1 Length	34.02 in (86.4 cm)
Package 1 Weight	35.78 lb(US) (16.23 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Pvc Free	
✓ Halogen Free Plastic Parts Product	

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>

Dimensions Drawings

Approximate Dimensions: Refer to Drawing 3362S

