





Automatic switch, PowerPacT J, 175A, 2 pole, 600VAC, 50kA, I-Line, magnetic, BC

JLA26000S174

Main

Product Or Component Type	Automatic switch
Range Of Product	PowerPact J
Trip Unit Technology	Magnetic
Circuit Breaker Type	Lframe

Complementary

Line Rated Current	250 A	
[Ue] Rated Operational Voltage	600 V AC	
Mounting Mode	I-Line	
Poles Description	2P	
Short-Circuit Withstand	125 kA 240 V UL 489 100 kA 480 V UL 489 50 kA 600 V UL 489 20 kA 250 V UL 489	
Breaking Capacity Code	L	
Electrical Connection	Lugs, load I-Line connection, line	
Awg Gauge	4 x AWG 3/0350 kcmil (aluminium/copper)	
Terminal Identifier	AL175JD	
Magnetic Tripping Current	Tripping Current 3125 A	
Tightening Torque	230.12 lbf.in (26 N.m) 0.040.15 in² (2595 mm²) (AWG 4AWG 4/0)	

Environment

Product Certifications	CE	
	UL Listed	
	CCC	
	IEC	
	NMX	
	CSA	

Ordering and shipping details

Category	01122-HL, JL I-LINE BREAKER/SWITCH
Discount Schedule	DE2
Returnability	No
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	5.00 lb(US) (2.268 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes
②	Pvc Free	

Certifications & Standards

California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration