





Automatic switch, PowerPacT J, 175A, 3 pole, 600VAC, 50kA, I-Line, magnetic, ABC

JLA36000S17

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,600.00 USD

Main

Product Or Component Type	Automatic switch
Range Of Product	PowerPact R
Trip Unit Technology	Magnetic
Circuit Breaker Type	Lframe

Complementary

Line Rated Current	175 A	
[Ue] Rated Operational Voltage	600 V AC	
Mounting Mode	Unit mount	
Poles Description	3P	
Short-Circuit Withstand	125 kA 240 V UL 489 100 kA 480 V UL 489 50 kA 600 V UL 489 20 kA 250 V UL 489	
Breaking Capacity Code	L	
Electrical Connection	Lugs, line Lugs, load	
Awg Gauge	x AWG 4AWG 4/0 (aluminium/copper)	
Terminal Identifier	AL175JD	
Magnetic Tripping Current	3125 A	
Height	7.52 in (191.01 mm)	
Width	2.74 in (69.60 mm)	
Depth	5 in (127.00 mm)	
Tightening Torque	230.12 lbf.in (26 N.m) 0.040.15 in² (2595 mm²) (AWG 4AWG 4/0)	

Environment

Product Certifications UL Listed

Ordering and shipping details

Category	US10DE201122
Discount Schedule	0DE2
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.38 in (13.653 cm)
Package 1 Width	8.13 in (20.638 cm)
Package 1 Length	14.63 in (37.148 cm)
Package 1 Weight	5.00 lb(US) (2.268 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov