Product data sheet

Specifications





Suppressor module, TeSys Deca, varistor, 110 to 250VAC

LA4DE2U

Product availability: Stock - Normally stocked in distribution facility

Price*: 31.44 USD

Main

Range	TeSys
Device Short Name	LA4D
Product Or Component Type	Suppressor module
Product Compatibility	4P LC1D80D115
	3P LC1D80D115

Complementary

Mounting Location	Тор	
Mounting Mode	By screws	
Suppressor Technology	Varistor (peak limiting)	
[Uc] Control Circuit Voltage	110250 V AC	
Maximum Peak Voltage	2 Uc	
Net Weight	0.04 lb(US) (0.018 kg)	

Environment

Standards	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 60947-5-1 UL 60947-5-1 GB/T 14048.5
Product Certifications	UL CSA
Ip Degree Of Protection	IP2XIEC 60529
Ambient Air Temperature For Operation	-13131 °F (-2555 °C)
Ambient Air Temperature For Storage	-40176 °F (-4080 °C)

Ordering and shipping details

Category	US10I1222341
Discount Schedule	0112
Gtin	3389110233124
Returnability	Yes
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.01 in (5.100 cm)
Package 1 Width	1.06 in (2.700 cm)
Package 1 Length	1.65 in (4.200 cm)
Package 1 Weight	0.46 oz (13.000 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	78
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	2.77 lb(US) (1.257 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations