





Circuit breaker, LA, 250A, 3 pole, 600VAC, 22kA, 250VDC, 10kA, lugs, thermal magnetic, shunt trip

LAL362501027

! Discontinued on: Mar 6, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

Complementally		
Line Rated Current	250 A	
Number Of Poles	3P	
Mounting Mode	Unit mount	
Magnetic Hold Current	1250 A	
Magnetic Tripping Current	2500 A	
Electrical Connection	Lugs, load Lugs, line	
Terminal Identifier	AL400LA	
Tightening Torque	115.06 lbf.in (13 N.m) 0.070.47 in² (42304 mm²) (AWG 1600 kcmil) 115.06 lbf.in (13 N.m) 0.070.20 in² (42127 mm²) (AWG 1250 kcmil)	
Height	11 in (279.40 mm)	
Width	6 in (152.40 mm)	
Depth	5.84 in (148.34 mm)	
Circuit Breaker Application	HACR rated	

Environment

Certifications	UL Listed IEC
	CSA

Ordering and shipping details

Category	US10DE200935
Discount Schedule	0DE2
Gtin	785901978947
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.44 in (21.433 cm)
Package 1 Width	11.13 in (28.258 cm)
Package 1 Length	17.13 in (43.498 cm)
Package 1 Weight	16.77 lb(US) (7.605 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov