





Circuit breaker, LA, 350A, 3 pole, 600VAC, 22kA, 250VDC, 10kA, lugs, thermal magnetic, shunt trip

LAL363501021

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 5,525.00 USD

#### Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

# **Complementary**

Line Rated Current	350 A
Number Of Poles	3P
Mounting Mode	Unit mount
Magnetic Hold Current	1750 A
Magnetic Tripping Current	3500 A
Electrical Connection	Lugs, load Lugs, line
Terminal Identifier	AL400LA
Tightening Torque	115.06 lbf.in (13 N.m) 0.070.47 in² (42304 mm²) (AWG 1600 kcmil) 115.06 lbf.in (13 N.m) 0.070.20 in² (42127 mm²) (AWG 1250 kcmil)
Height	11 in (279.40 mm)
Width	6 in (152.40 mm)
Depth	5.84 in (148.34 mm)
Circuit Breaker Application	HACR rated

#### **Environment**

Certifications	IEC UL Listed
	CSA

## Ordering and shipping details

Category	US10DE200935
Discount Schedule	0DE2
Gtin	785901339489
Returnability	No
Country Of Origin	MX

## **Packing Units**

<b>Unit Type Of</b>	Package 1	PCE
---------------------	-----------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	9.00 in (22.86 cm)
Package 1 Width	11.60 in (29.464 cm)
Package 1 Length	17.50 in (44.45 cm)
Package 1 Weight	16.77 lb(US) (7.605 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov