





Circuit breaker, LA, 300A, 3 pole, 600VAC, 22kA, 250VDC, unit mount, thermal magnetic

LAP36300

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 4,619.00 USD

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Magnetic

Complementary

•	
Line Rated Current	300 A
Number Of Poles	3P
Breaking Capacity Code	A
Mounting Mode	Unit mount
Wiring Configuration	3-wire
Magnetic Hold Current	1500 A
Magnetic Tripping Current	3000 A
Electrical Connection	Lugs, load Terminal, line
Terminal Identifier	AL400LA
Height	11 in (279.40 mm)
Width	6 in (152.40 mm)
Depth	5.84 in (148.34 mm)
Circuit Breaker Application	HACR rated

Environment

Certifications	IEC	
	CSA	
	UL Listed	

Ordering and shipping details

Category	US10DE200935
Discount Schedule	0DE2
Gtin	785901423980
Returnability	Yes
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.40 in (23.876 cm)
Package 1 Width	10.80 in (27.432 cm)
Package 1 Length	15.80 in (40.132 cm)
Package 1 Weight	15.67 lb(US) (7.11 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free
	Rohs Exemption Information Yes
	Pvc Free
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov