

# Product data sheet

Specifications

## Control terminal block, reversing motor starter, TeSys Ultra



LU9M1

Product availability: Stock - Normally stocked in distribution facility

Price\*: 15.00 USD

### Main

Range	TeSys
Device Short Name	LU9M
Product Or Component Type	Control terminal block
Product Compatibility	LU2MB0.. LU2BB0.. LU2BA0.. LU6MB0..

### Complementary

Net Weight	0.06 lb(US) (0.025 kg)
Tightening Torque	Control circuit 7.08...10.62 lbf.in (0.8...1.2 N.m) flat 0.20 in (5 mm) Control circuit 7.08...10.62 lbf.in (0.8...1.2 N.m) Philips No 2 0.20 in (5 mm) Power circuit 16.82...22.13 lbf.in (1.9...2.5 N.m) flat 0.24 in (6 mm) Power circuit 16.82...22.13 lbf.in (1.9...2.5 N.m) Philips No 2 0.24 in (6 mm) Power circuit 16.82...22.13 lbf.in (1.9...2.5 N.m) pozidriv No 2 0.24 in (6 mm)

### Ordering and shipping details

Category	US10I1122399
Discount Schedule	0I11
Gtin	3389110367553
Returnability	Yes
Country Of Origin	SE

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	2.36 in (6.0 cm)
Package 1 Length	2.36 in (6.0 cm)
Package 1 Weight	0.74 oz (21.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	30
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	29.77 oz (844.0 g)
------------------	--------------------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>	