

Product data sheet

Specifications



EBE - EnOcean 868MHz - Indoor humidity and temperature sensor 0-40°C

LSS10020041

 **Discontinued on:** Oct 28, 2022

 **Discontinued**

Main

Range	EcoStruxure Building Expert
Product Name	EnOcean
Product Or Component Type	Humidity sensor Temperature sensor

Complementary

Type Of Measurement	Temperature - 0...40 °C +/- 0.5 °C 0.16 °C Humidity - 5...100 % +/- 5 % 0.4 %
Type Of Installation	Indoor
Device Mounting	Surface
Transmission Frequency	868.3 MHz
Transmitting Range	30 m with walls 300 m without walls
Supply	Solar cell >100 lux average per day
Nominal Output Power	0.01 W
Ip Degree Of Protection	IP40
Height	0.98 in (25 mm)
Width	3.07 in (78 mm)
Market Segment	Small buildings

Environment

Ambient Air Temperature For Storage	-4...140 °F (-20...60 °C)
Directives	1999/5/EC - R&TTE directive

Ordering and shipping details

Gtin	7332552010545
------	---------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	3.11 in (7.9 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	1.02 in (2.6 cm)
Package 1 Weight	1.13 oz (32.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	36
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.54 lb(US) (1.607 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div><div>Yes</div></div>	
<div><div>Eu Rohs Directive</div><div>Compliant</div><div>EU RoHS Declaration</div></div>	
<div><div>China Rohs Regulation</div><div>China RoHS declaration</div></div>	