Product data sheet

Specifications





Switch disconnector, MasterPact MTZ2 10HF, 1000A, 187kA/ 690VAC 50/60Hz (Icm), 4P, fixed

LV848027

Main

Range	MasterPact
Product Or Component Type	Switch disconnector
Device Application	Distribution
Switch-Disconnector Name	MasterPact MTZ2 10 HF
Poles Description	4P
Network Type	AC
Network Frequency	50/60 Hz

Complementary

Push-button
Fixed
690 V AC 50/60 Hz EN/IEC 60947-3
1000 A AC 50/60 Hz 690 V
1000 V AC 50/60 Hz EN/IEC 60947-3
12 kVEN/IEC 60947-3
50 kA 3 s EN/IEC 60947-3 85 kA 1 s EN/IEC 60947-3
187 kA peak 220690 V AC 50/60 Hz
AC-23A AC-3
HF
Yes EN/IEC 60947-3
Yes
No
25000 cycles with periodic preventive maintenance EN/IEC 60947-3
AC-23A 10000 cycles 440 V AC 50/60 Hz EN/IEC 60947-3 AC-23A 10000 cycles 690 V AC 50/60 Hz EN/IEC 60947-3 AC-3 6000 cycles 440 V AC 50/60 Hz EN/IEC 60947-3 AC-3 6000 cycles 690 V AC 50/60 Hz EN/IEC 60947-3
4.53 in (115 mm)
13.86 in (352 mm)
21.14 in (537 mm)
11.81 in (300 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Net Weight	143.30 lb(US) (65 kg)
Standards	EN/IEC 60947-3
Product Certifications	IECEE CB Scheme
Ip Degree Of Protection	IP30
Pollution Degree	3 EN/IEC 60947-4-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)

Ordering and shipping details

Gtin

3606480817397

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.86 in (35.2 cm)
Package 1 Width	21.14 in (53.7 cm)
Package 1 Length	11.81 in (30.0 cm)
Package 1 Weight	143.30 lb(US) (65.0 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov