


Product data sheet

Specifications



TeSys Deca - contactor coil - LXD3 - 127 V AC 50/60 Hz for 40â€¦ 65 A contactor

LXD3FC7

⚠ Discontinued on: Oct 8, 2021

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LXD3
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	127 V AC 50/60 Hz
Average Resistance	60.29 Ohm 68 °F (20 °C)
Inductance Of Closed Circuit	3.34 H
Product Compatibility	LC1D40A...D65A LC1DT80A LC1DT60A
Mechanical Durability	6 Mcycles
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out: 0.3...0.6 Uc at 50/60 Hz (at <140 °F (60 °C)) Operational: 0.8...1.1 Uc at 50 Hz (at <140 °F (60 °C)) Operational: 0.85...1.1 Uc at 60 Hz (at <140 °F (60 °C))
Inrush Power In Va	160 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 160 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	15 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 15 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	4...5 W 50/60 Hz

Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Net Weight	0.15 lb(US) (0.07 kg)

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	3389119410380
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.28 in (5.8 cm)
Package 1 Width	2.28 in (5.8 cm)
Package 1 Length	3.86 in (9.8 cm)
Package 1 Weight	5.64 oz (160 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Pvc Free

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

California Proposition 65

WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
