

# Product data sheet

Specifications



Surge protection module,  
Surgelogic, MA, 160kA, 120/240  
VAC, 1 phase, 3 wire, SPD type 2

MA1IMA16

Product availability: Stock - Normally stocked in distribution facility

Price\*: 625.00 USD

## Main

Product	Surge protection module
Range	Surgelogic
Device Short Name	IMA
Accessory Category	Replacement part

## Complementary

Voltage Rating	120/240 V AC
Mcov	150 V
Sccr	200 kA
Surge Current	160 kA per phase
Nominal Discharge Current	20 kA
Number Of Phases	1 phase
Wiring Configuration	3-wire
Connection	Terminals
Local Signalling	Status LED green normal operation
Provided Equipment	Alarm enable/disable switch
Mounting Support	Panel mounting
Height	6.25 in (158.8 mm)
Width	3.26 in (82.8 mm)
Depth	2.69 in (68.3 mm)

## Environment

Ambient Operating	149 °F (65 °C)
Enclosure Rating	NEMA 2
Enclosure Material	Black Plastic
Standards	UL 1449:ed. 4 UL 1283:ed. 5 CSA C22.2 No 8:1986 ANSI/IEEE C62.41 ANSI/IEEE C62.45 NEC 285

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	US1DE1B08467
Discount Schedule	DE1B
Gtin	785901292920
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.60 in (11.684 cm)
Package 1 Width	5.60 in (14.224 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	32.00 oz (907.18 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability


**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>