Product data sheet

Specifications



Surge protection module, Surgelogic, MA, 120kA, 120/240 VAC, 3 phase, 4 wire, SPD type 2

MA3IMA12

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 600.00 USD

Main

Product	Surge protection module
Range	Surgelogic
Device Short Name	IMA
Accessory Category	Replacement part

Complementary

Complementary	
Voltage Rating	120/240 V AC
Мсоч	150 V
Sccr	200 kA
Surge Current	120 kA per phase
Nominal Discharge Current	20 kA
Number Of Phases	3 phase
Wiring Configuration	4-wire
Connection	Terminals
Local Signalling	Status LED green normal operation
Provided Equipment	Alarm enable/disable switch
Mounting Support	Panel mounting
Height	6.25 in (158.8 mm)
Width	3.26 in (82.8 mm)
Depth	2.69 in (68.3 mm)

Environment

Ambient Operating	149 °F (65 °C)
Enclosure Rating	NEMA 2
Enclosure Material	Black Plastic
Standards	UL 1449:ed. 4 UL 1283:ed. 5 CSA C22.2 No 8:1986 ANSI/IEEE C62.41 ANSI/IEEE C62.45 NEC 285

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	US1DE1B08467
Discount Schedule	DE1B
Gtin	785901292944
Returnability	No
Country Of Origin	US

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.26 in (15.9 cm)
Package 1 Width	3.27 in (8.3 cm)
Package 1 Length	2.68 in (6.8 cm)
Package 1 Weight	3.00 lb(US) (1.361 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov