

Product data sheet

Specifications



Meter center, MP Meter-Pak, 2 sockets, no bypass, 5 jaws, 200A bus, 125A max breaker rating, ringless

MPR22125

Product availability: Stock - Normally stocked in distribution facility

Price*: 995.00 USD

Main

Product	Meter Center
Socket Rating	125 A
Main Type	Main Lugs
Number Of Jaws	5
Number Of Meter Sockets	2
Socket Type	Ringless

Complementary

Main Rating	200 A
Bus Rating	200 A
Certifications	UL Listed
Type	Meter-Pak
Busbar Material	Aluminium: busbar
Bypass Type	No bypass
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	120/240 V AC
Mounting	Surface
Phase	1 phase
Service Feed Location	UG OH
Wire Size	AWG 4...250 kcmil 1 aluminium AWG 4...250 kcmil 1 copper
Wire Configuration	3-wire
Height	37.50 in (952.50 mm)
Width	12.28 in (311.91 mm)
Depth	7.28 in (184.91 mm)

Ordering and shipping details

Category	US10DE400021
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	0DE4
Gtin	785901208051
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.30 in (21.082 cm)
Package 1 Width	12.50 in (31.75 cm)
Package 1 Length	38.80 in (98.552 cm)
Package 1 Weight	42.27 lb(US) (19.173 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov