Product data sheet

Specifications

SQUARE D





Panelboard interior, NQ, main lugs, 400A, Al bus, 42 pole spaces, 3 phase, 4 wire, 240VAC, 48VDC

NQ442L4

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,012.00 USD

Main

Panelboard Type	Main lugs
Branch Circuit Breaker Type	QOB
	QOB-VH
	QHB
Busbar Material	Aluminium

Complementary

42
50 in (1270.00 mm)
20 in (508.00 mm)
5.75 in (146.05 mm) NEMA 1
6.5 in (165.10 mm) NEMA 3R/5/12
400 A
10 kA
22 kA
65 kA
4-wire
3 phase
240 V AC
48 V DC
Lug line AWG 1/0750 kcmil aluminium
Lug neutral AWG 1/0750 kcmil aluminium
274.99300.04 lbf.in (31.0733.90 N.m) 0.080.59 in ² (53.48380 mm ²) (AWG
1/0750 kcmil)
274.99300.04 lbf.in (31.0733.90 N.m) 0.080.27 in ² (53.48177.3 mm ²) (AWG
1/0350 kcmil)
549.98 lbf.in (62.14 N.m) 0.080.59 in ² (53.48380 mm ²) (AWG 1/0750 kcmil)
549.98 lbf.in (62.14 N.m) 0.080.24 in² (53.48152 mm²) (AWG 1/0300 kcmil)
375.01 lbf.in (42.37 N.m) 0.080.59 in ² (53.48380 mm ²) (AWG 1/0750 kcmil)
375.01 lbf.in (42.37 N.m) 0.080.24 in ² (53.48152 mm ²) (AWG 1/0300 kcmil)
45 in (1143.00 mm)
10.44 in (265.18 mm)

Environment

Standards

CSA UL

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1PE1A09151
Discount Schedule	PE1A
Gtin	785901507895
Returnability	Yes
Country Of Origin	МХ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.18 in (15.7 cm)
Package 1 Width	14.09 in (35.8 cm)
Package 1 Length	50.00 in (127.0 cm)
Package 1 Weight	22.80 lb(US) (10.34 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	15
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	42.00 in (106.68 cm)
Package 2 Length	60.00 in (152.4 cm)
Package 2 Weight	465.42 lb(US) (211.11 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc


Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Approximate Dimensions



* For Type 3R enclosure, increase height dimension by 12.00 / [305]