Product data sheet

() Discontinued

Specifications



Spacial SF rear panel internal fixing - 2000x800 mm

NSYBPI208

() Discontinued on: Sep 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Rear panel
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Rear of enclosure
Quantity Per Set	Set of 1

Complementary

	5
Range Compatibility	Spacial Spacial SF
Device Composition	fixing elements 1 rear panel
Material	steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By fixing element - from the inside of enclosure
Height	Nominal 78.74 in (2000 mm)
Width	Nominal 31.50 in (800 mm)

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485125855
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6.0 cm)
Package 1 Width	33.86 in (86.0 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Length	79.13 in (201.0 cm)
Package 1 Weight	48.50 lb(US) (22.0 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	12
Package 2 Height	20.87 in (53.0 cm)
Package 2 Width	81.89 in (208.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	632.73 lb(US) (287.0 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations